

[Find by Feature](#)
[Browse by Category](#)
[Share](#)

[Search →](#)

Enter part number or keyword

[Search Results \(0\)](#)
[Search Options](#)

Select a product type to narrow your search:

Terminal ▼

Results with your selections: --

Blade size [mm] ▼

Terminal family ▼

Material ▼

Plating ▼

Gender ▼

Sealed ▼

Inside Ring Diameter [mm] ▼

Outside Ring Diameter [mm] ▼

Minimum Cable Core Cross Section [mm²] ▼

Maximum Cable Core Cross Section [mm²] ▼

Minimum Cable Diameter [mm] ▼

Maximum Cable Diameter [mm] ▼

[Clear](#)
[Search →](#)

Male Metri-Pack 280 Tin Plated Terminal, Cable Insulation Range 2.00 - 1.35 mm Part #12020782

[Question about this product?](#)

[Attributes](#)
[Documents \(6\)](#)

Part #:	12020782
Description:	Male Metri-Pack 280 Tin Plated Terminal, Cable Insulation Range 2.00 - 1.35 mm
Product Type:	Terminal
Status:	Active
Blade size [mm]:	2.8
Terminal family:	Metri-Pack
Series:	280
Gender:	Male
Sealed:	Unsealed
Material:	Tin Brass
Plating:	Tin
Minimum Cable Core Cross Section [mm²]:	0.35
Maximum Cable Core Cross Section [mm²]:	0.35
Minimum Cable Diameter [mm]:	1.35
Maximum Cable Diameter [mm]:	2.00
Current range [A]:	30
Temperature range [°C]:	-40 to 125

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.