Part Number : 1301550192
Product Description : Woodhead Heavy Duty, Molded Multi-Pin Plug, 60A, 6/4 SOOW Cable, 1.83m (6.0') Cord Length
Series Number : 130155
Status : Active
Product Category : Wiring Devices
Engineering Part Number : DW760-60M38



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130155
Description	Woodhead Heavy Duty, Molded Multi-Pin Plug, 60A, 6/4 SOOW Cable, 1.83m (6.0') Cord Length
IP Rating	IP67
NEMA Configuration	Non-NEMA
Product Name	Watertite Extreme
Specialty	Molded Mutli-Pin
Type	Plug
UPC	78172541943

Electrical

Current - Maximum per Contact	60.0A
GFCI	No
Voltage - Maximum	600V

Physical

Cord Type	6/4 SOOW
Flange	No
Flip Lid	No
Gender	Male
Length	1.83m (6.0')
Lighted Connector	No
Locking Blade	No
Poles	4
Receptacle Type	N/A

Downloaded from Arrow.com.