
TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

TERMINALS









✔ Active

PRODUCT DRAWING
English

3D PDF

TE CONNECTIVITY (TE)

TAB 4.8X0.8

1564228-2

TE Internal Number: 1564228-2

Always EU RoHS/ELV Compliant

Terminal Style **Pin/Tab**

Mating Tab Width **4.8 mm [.189 in]**

Mating Tab Thickness **.8 mm [.031 in]**

Terminal Transmits **25 – 40 A (Power)**

Primary Locking Feature **None**

Product Drawings

TAB 4.8 X 0.8 WITH ACTION PIN L.P. Flachstecker 4,8 X 0,8 Mit ACTION PIN Einzelt
PDF **(TIFF AVAILABLE)**
English

TAB 4.8 X 0.8 WITH ACTION PIN L.P. Flachstecker 4,8 X 0,8 Mit ACTION PIN Einzelt
PDF **(TIFF AVAILABLE)**
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Primary Locking Feature **None**

Downloaded from Arrow.com.

	Wire Type	**Copper**
Contact Features	Terminal Style	**Pin/Tab**
	Mating Tab Width	**4.8 mm [.189 in]**
	Mating Tab Thickness	**.8 mm [.031 in]**
	Interface Plating	**Tin (Sn)**
	Typical Current Rating (A)	**36**
Termination Features	Termination Method	**Press-Fit**
Usage Conditions	Operating Temperature Range	**-40 – 125 °C [-40 – 257 °F]**
Other	Terminal Transmits	**25 – 40 A (Power)**

Product Compliance

Statement of Compliance
PDF

VIEW ALL PRODUCT COMPLIANCE

Downloaded from Arrow.com.