



**Part Number :** 1300940515

**Product Description :** Bus-Drop Support Grip, Locking Bale, Cable Diameter 10.16-14.22mm (.400-.560"), Approximate Break Strength 226.80kg (500 lbs)

**Series Number :** 130094

**Status :** Active

**Product Category :** Cable Grips

**Engineering Number :** 36585



## Documents & Resources

### Drawings

[PK-130227-004-001.pdf](#)

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Locking Bale, Cable Diameter 10.16-14.22mm (.400-.560"), Approximate Break Strength 226.80kg (500 lbs)
Product Name	Service-Drop
Type	Support Grip
UPC	78678835813

#### Agency

CSA	LR32159
-----	---------

#### Physical

Approximate Break Strength	226.80kg (500 lbs)
Bale Length	0.305m (12.00")
Body Style	Straight
Cable Diameter	10.16-14.22mm (.400-.560")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.127m (5.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A