Part Number : 936010154
Product Description : Heavy-Duty Crimp Contact Insert, Male, 16-Pole, 16A, Numbered 17-32, for Crimp Contacts, Size 16A «66x16»
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7216.4463.0



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Crimp Contact Insert, Male, 16-Pole, 16A, Numbered 17-32, for Crimp Contacts, Size 16A «66x16»
Component Type	Inserts - Crimp Contact
Insert Series	S-AC
Product Name	Heavy-Duty Connectors
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, EUROMAP, UL 1977
UPC	887191873725

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V

Physical

Component Size	16A «66X16»
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	37.000/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	16

Downloaded from Arrow.com.

Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Crimp Contact Insert, Female, 16-Pole, 16A, Numbered 17-32, for Crimp Contacts, Size 16A «66x16»	936010152

Use with Part(s)

Description	Part Number
Use With	Turned Contacts - Male

Downloaded from Arrow.com.