Specifications



Photo is representative





Eaton FP0805R1-R10-R

Eaton FP0805 inductor, 0.1 uH, 65 A Irms, 50 A ISAT, 0.199 mΩ resistance, SMT mounting, Ferrite, 2-pins, 950 qty.

General specifications	
PRODUCT NAME	Eaton FP0805 inductor
CATALOG NUMBER	FP0805R1-R10-R
UPC	051712543903
PRODUCT LENGTH/DEPTH	7.62 mm
PRODUCT HEIGHT	4.96 mm
PRODUCT WIDTH	7.49 mm
PRODUCT WEIGHT	1.06 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	65 A
ISAT	50 A
PACKAGE QUANTITY	950
MATERIAL	Ferrite
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.199 mΩ
SERIES	FP0805

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - FP0805R1-R10-R Eaton FP0805 power inductor data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.