



Pliers

Home > 6" Long Chain Nose Solid Joint Side Cutting Pliers

6" Long Chain Nose Solid Joint Side Cutting Pliers

Catalog Number: 8546CVSMLNN

★★★★★ (0) [Write a review](#)

[Ask a question](#)

BUY NOW



[Download Images](#)

Share:   

Overview

6-5/8" Long Chain Nose Side Cutting Solid Joint Pliers, Cushion Grip

Features

- 6" Long Chain Nose Solid Joint Side Cutting Pliers
 - Designed for Reaching Confined Areas
 - Long Chain Nose with Fine Serrated Jaws to Make Wire Loops and Bends
 - Electronically Induction Hardened Hand-Honed, Keen Side Cutting Edges
 - Made of Forged Alloy Tool Steel
 - Individually Tested for Strength and Cutting Ability
 - Polished Head
 - Red Double Dipped Cushion Handle Grips
 - Spring Keeps Jaws Open

Specifications

Foreign Trade Code	8203206030
UPC	037103324078
Set	No
Overall Length	6.625 in
Handle Material	Double Dip Cushion Grip
Edge Type/Cut Capacity	Std./14 AWG
Jaw Length	1-7/8 in
Jaw Thickness	3/8 in
Jaw Width	11/16 in
Packaging	No
Weight (Catalog)	0.380 lb

[+ Reviews | Questions](#)



Trusted by the Trades.

MERCHANDISE

Apex Tool Group

910 Ridgebrook Road

Suite 200

Sparks, Maryland 21152

(800) 821-8814

Tools

Brands

New Products

Featured Products

Shipping Information

Where to Buy

Media Center

About

Warranty

Contact Us

Privacy Policy

California And Nevada
Privacy Notice

Distributor Login

Reseller Policies



© 2021 Apex Tool Group, LLC. All rights reserved.