



## Technical Data

17.07.2023

Heat shrinkable tubing 2:1 - PVC  
LVR

**LVR-4.8/2.4**

**Article Number 344-00480**



Material:	Flexible Polyvinyl Chloride, cadmium free (PVC)
Colour:	Black (BK)
Supplied Ø D min.:	4.8 mm
Recov. Ø d max.:	2.4 mm
Wall (WT):	0.50 mm
Shrink Ratio:	2:1
Longitudinal Change After Shrinkage:	+/-10% max
Min. Shrink Temperature - °C:	+80 °C
Flammability:	UL 224 VW-1
Operating Temperature :	-30 °C to +105 °C
Dielectric Strength:	22 kV/mm
Specifications:	ANSI/UL 224
Shelf Life:	12 months



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved