

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal cover, 1 strip covers up to 12 terminal points, for ME-BUS male side, (female side)



Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

Commercial data

Item number	2935959
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHACZ
GTIN	4017918611668
Weight per piece (including packing)	5.24 g
Weight per piece (excluding packing)	4.67 g
Customs tariff number	39269097
Country of origin	DE

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Technical data

Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

Dimensions

Width	14.5 mm
Height	91.1 mm
Depth	17.9 mm
Depth from top edge of DIN rail	15.2 mm

Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Snap in
---------------	---------

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2935959>



UL Recognized

Approval ID: E240868

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com