

Printed On 2 Aug 2022 17:23 (China Standard Time) from FG086075






D

B


A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
	AI	REVISED	02AUG2022	J. J. N. S.



SCALE 10:1



RECOMMENDED P.C.B LAYOUT TOLERANCE ±0.05

1. PART NUMBER: 2343297-2.
2. MATERIAL: SUS301 K1500. THICKNESS=0.12mm.
3. FINISH : 2.0~7.6um NICKEL UNDERLAYER ALL OVER.
0.38um MIN. GOLD PLATING ON CONTACT AREA.
0.08~0.6um GOLD PLATING ON SOLDER AREA.
4. NORMAL FORCE: 0.7N MIN(INITIAL) AT WORKING RANGE.
0.6N MIN AFTER DURABILITY EVALUATION.
5. WORKING RANGE: 2.30mm ~ 3.50 mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE J1 20SEP2018	TE Connectivity	
		CHK WENKE HF 20SEP2018		
		APVD WENKE HF 20SEP2018	NAME 4.0H SPRING FINGER	
DIMENSIONS: mm		PRODUCT SPEC		
		APPLICATION SPEC		
		WEIGHT		
MATERIAL		CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779
			DRAWING NO C=2343297	RESTRICTED TO
			SCALE 1:1	SHEET 1 OF 2
				REV A1

D

C

B

A

Printed On 2 Aug 2022 17:23 (China Standard Time) from FG086075

D

B

A




D

C

B

A


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20		REVISIONS	
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.		P	LTR
						DESCRIPTION	
						DATE	DWN
						APVD	



WITH PRODUCT CHARGE
1700 EA/REEL
NO EMPTY POCKETS
ARE PERMITTED

COVER TAPE
100mm MIN WITHOUT CHARGE

USER DIRECTION OF UNREELING →



NOTE:
1. PACKAGE SPEC EIA-481-D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JONE JJ	20SEP2018	 TE Connectivity							
		CHK	WENKE HF	20SEP2018								
		APVD	WENKE HF	20SEP2018								
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME 4.0H SPRING FINGER							
mm		± -										
		0-PLC ± -			PRODUCT SPEC -							
		1-PLC ±0.1										
		2-PLC ±0.01										
		3-PLC ±0.001										
		4-PLC ±0.0001										
MATERIAL		FINISH			SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
-		-			A3		00779		C=2343297		-	
					WEIGHT							
					-							
					CUSTOMER DRAWING				SCALE		SHEET	
									1:5		2 OF 2	
											REV A1	