
MALLORY Mallory Sonalert Products Inc.	Part # PT-1540PQ
Sales Outline Drawing	Revision G

May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.
NO CIRCUITRY

Resonant Frequency (Hz)	4000 ± 500
Operating Voltage (Vp-p/max)	25
Rated Voltage (Vp-p)	5.0
Current Consumption (mA/max)	1.5 at Rated Voltage
Sound Pressure Level (dB/min)	85 at 10cm at Rated voltage
Capacitance (pF)	14,000 ±30% at 120Hz
Operating Temperature (°C)	-20 ~ +100
Storage Temperature (°C)	-30 ~ +110
Housing	PBT1200 UL94HB plastic resin (Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	1.6
Condition by wave soldering (°C)	260 ±5 / within 5 sec
Condition by hand soldering (°C)	350 ±20 / within 5 sec
Options	For other options contact factory

Dimensions: (units: mm) PS: Vp-p = 1/2duty, square wave **ROHS Compliant**



4411 South High School Road, Indianapolis, Indiana 46241 USA ● Phone (317) 612-1000 ● Fax (317) 612-1010 ● http://www.mspindy.com

Downloaded from Arrow.com.