






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/6/14	



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Steel, Tin plated

Clinch Nut: Brass, Nickel plated

Boardlock: Brass, Tin plated

Screwlock: Copper Alloy Nickel plated

Plating:

30u" Gold over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max @ DC 100 mA

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant

Positions	DIMENSIONS						
	A	B	C	D	E	F	G
15	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.756 [19.20]	.090 [2.29]	.045 [1.145]	.277 [7.04]
26	.994 [25.25]	1.311 [33.30]	1.543 [39.20]	1.091 [27.70]	.090 [2.29]	.045 [1.145]	.271 [6.88]
44	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]	.090 [2.29]	.045 [1.145]	.271 [6.88]
62	2.182 [55.43]	2.500 [63.50]	2.732 [69.40]	2.256 [57.30]	.095 [2.41]	.047 [1.205]	.276 [7.00]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	6/6/14
CHECKED	LW	6/6/14
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE		
HIGH DENSITY D-SUB PLUG, PCB TAILS RIVETED #4-40 STANDOFFS W/BOARDLOCKS		
SIZE X	PART NO. HDTXX-PT-BL-JS-30	REV. -
REF: S00087T	SCALE: NTS	SHEET 1 OF 1

