166635-1 Product Details

Live Product Chat

No Image Available

166635-1

TE Part Number: 166635-1
Active
Add to Part List

Eurocard and RS-System Contacts

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact Type = Snap-In
- Pin
- Straight Contact Shape
- Terminate To Cable
- Wire Range = 0.12-0.50² [26-20] mm [AWG]

View all Features | Find Similar Products

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples NEW!

Documentation & Additional Information

Product Drawings:
- crimp-on snap-in tab receptacle (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Pin/Socket = Pin
- Wire Insulation Diameter (mm [in]) = 1.10 - 1.80 [0.043 - 0.071]
- Make First / Break Last = No
- DIN Level = I
- Used For = Type F Vertical Housing
- Wire Termination Type = Crimp

Mechanical Attachment:
- Contact Retention in Housing = Crimp Snap-In

Body Related Features:
- Wire Range (mm [AWG]) = 0.12-0.50² [26-20]

Contact Related Features:
- Contact Type = Snap-In
- Contact Shape = Straight
- Contact Material = Brass

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:
- Terminate To = Cable

Packaging Related Features:
- Packaging Method = Loose Piece

Other:
- Brand = AMP

© 2008 Tyco Electronics Corporation All Rights Reserved
Downloaded from Arrow.com.