



YA2C2TC38, 2 AWG, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Long Barrel

By Burndy
Catalog # [YA2C2TC38](#)



2 AWG, Cu Compression Lug, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel, Brown / 10 Index

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
--------------------------------------	---

Connector Type LONG BARREL

Current

Voltage - Maximum	35000
Voltage Rating	35 kV

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.42 in
Dimension - L Length Overall mm	87 mm
Dimension - Pad Width inch	0.60 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - B Length inch	1.25 in
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.42 in
Dimension - D inch	1.84 in
Dimension - N inch	0.41 in

General

Die Index	10
Trade Name	HYLUG™
Sub Brand	HYLUG
Color Code	Brown
Physical Attribute - Tongue Type	Standard
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	Long Barrel, Tin Plated
UPC 12 Digit	781810503515

UPC 14 Digit GTIN 00781810503515
Material COPPER
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 781810503515

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)
[Installation Manual \[French, English\]](#)

Logistics

Minimum Pack Quantity 1
Carton Quantity 25



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YA2C2TC38-SPEC-EN | REV 4/2026