



Part Number : 936040204

Product Description : GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 160 x 160 x 90mm Outside Dimensions, Sandblasted

Series Number : 93604

Status : Obsolete

Product Category : Die-cast Enclosures

Engineering Number : 8100.8219.0



Documents & Resources

Product Environment Compliance

Compliance

| | |
|--------------------|--------------------|
| GADSL/IMDS | Product not active |
| China RoHS | Product not active |
| EU ELV | Product not active |
| Low-Halogen Status | Product not active |
| REACH SVHC | Product not active |
| EU RoHS | Product not active |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|--|
| Status | Obsolete |
| Category | Die-cast Enclosures |
| Series | 93604 |
| Description | GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 160 x 160 x 90mm Outside Dimensions, Sandblasted |
| IP Rating | IP66, IP69 |
| Product Name | GWconnect |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2 |
| Type | Sandblasted |
| UPC | 887191879291 |

Physical

| | |
|-------------------------------|------------------------|
| Internal Dimensions | 151 x 151 x 84mm |
| Material - Enclosure | Die-cast Aluminum |
| Mounting Style | Internal Through Holes |
| Net Weight | 1595.000/g |
| Outside Dimensions | 160 x 160 x 90mm |
| Packaging Type | Carton |
| Temperature Range - Operating | -40° to +125°C |

Mates With / Use With

Use with Part(s)

| Description | Part Number |
|-------------|---|
| Use With | DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals |

Obsolete