C2G

9ft (2.7m) Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Orange

Part No. 04020



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

Specifications

General Info

Product Line	C2G	Color	Orange
UPC Number	757120040200	Country Of Origin	Vietnam
Features	PoE (Power Over Ethernet)	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	9.0 FT	Cable Length	9 ft
Outside Diameter	5.69 mm		

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes

Additional Information

RoHS Compliant	Yes

Downloaded from Arrow.com.

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Application	Cat6
Wiring Scheme	T568B	Wire Gauge	24 AWG
Shielded/Unshielded Cable	Unshielded	Shield Type	UTP
Cable Type	Ethernet Patch Cable	Jacket Rating	Standard / Non-Rated
Cable Diameter	6.2 mm	Connector Type	Booted, Snagless
Indoor/Outdoor	Indoor	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male		

Downloaded from Arrow.com.