



Part Number : [1731130231](#)
Product Description : FCT High-Density D-Sub Connector, Female, Straight, PCB Through Hole, Gold Plating, 5.60mm Snap-in Bolt, 44 Circuits
Series Number : 173113
Status : Active
Product Category : D-Sub Connectors
Engineering Number : CT25-44S1-0981




Documents & Resources

Drawings

- [1731130231 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	<div></div> per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173113
Description	FCT High-Density D-Sub Connector, Female, Straight, PCB Through Hole, Gold Plating, 5.60mm Snap-in Bolt, 44 Circuits
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	High Density
UPC	191130138852

Electrical

Current - Maximum per Contact	3.0A
Shielded	Yes

Physical

Circuits (Loaded)	44
Circuits (maximum)	44
Color - Resin	Black
Durability (mating cycles min)	50
Gender	Female
Material - Contact	Copper Alloy

Material - Resin	PBT
Material - Shell	Steel
Net Weight	12.600/g
Number of Rows	3
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	9.50mm
Pitch - Mating Interface	1.98mm
Pitch - Termination Interface	1.98mm
Plating - Contact	Gold over Nickel
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +105°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT High-Density D-Sub, Size 3, 44 Position, Plug

This document was generated on Sep 10, 2025