

[Passive Components](#) > [Resistors](#) > [Fixed Resistors](#) > [Surface Mount Resistors](#)

MRS 4X 0603 33K 0.1% 25PPM

✓ **ACTIVE**

Holsworthy

TE Part # **MRS33KBF**

TE Internal #: **1-1624122-0**

Resistor Type : **General Purpose Resistor**

Number of Terminations : **8**

Size Code : **1206**

Packaging Method : **Taped & Reeled**

Tolerance : **.1%**

 [Add to List](#) ▼

[Similar Products](#)



ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America ▼

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

CAD Files

3D PDF

 [3D_CVM_CVM_1-1624122-0_BA.pdf](#) 3D

Customer View Model

 [ENG_CVM_CVM_1-1624122-0_BA.2d_dxf.zip](#)

English

 [ENG_CVM_CVM_1-1624122-0_BA.3d_igs.zip](#)

English

 [ENG_CVM_CVM_1-1624122-0_BA.3d_stp.zip](#)

English

Catalog Pages/Data Sheets



[ENG_CS_1309350_PASSIVE_COMPONENT_0807.pdf](#)

f English

 [ENG_DS_1773252_E.pdf](#) English

Product Environmental Compliance

TE Material Declaration

 [ENG_PC_MD_1-1624122-0_A_MD_1-1624122-0_09082014849_dmtc.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Resistor Type : General Purpose Resistor
	Size Code : 1206
	Product Type : Fixed Resistor
Configuration Features	Number of Resistors : 4
Electrical Characteristics	Tolerance : .1%
	Resistance Range (Ω): 1kΩ – 1MΩ
	Resistance (Ω): 33K
	Power Rating (W): .063
Termination Features	Number of Terminations : 8
	Termination Type : Solder
Mechanical Attachment	Mount Style : Surface Mount
Dimensions	Dimensions (mm): 3.2 x .55 x 1.6
Usage Conditions	Temperature Coefficient (ppm/°C): ±25
Packaging Features	Packaging Method : Taped & Reeled
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

> [Contact Product Support](#)

Customers Also Bought



TE Part # RN73C1J16R9BTG
RN 0603 16R9 0.1%
100PM CUT LENGTH



TE Part # 2007853-3
IMP100S, H, V5P10C,
UG, LEW39, 5.5



TE Part # 1734098-6
Champ050 60p A/P
RCPT 25CL PB



TE Part # 2007854-3
IMP100S, H, V5P10C,
UG, DEW39, 5.5

About TE Connectivity

For Partners

Customer Support

CALL US

LIVE CHAT

United States

Our Company

Events

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of Sale

Distributors

Suppliers



Email or Call Us



Find Authorized Distributors



What's New on TE.com



Product FAQs

Select Country & Language

United States (EN)

Germany (DE)

China (中文)

Japan (日本語)

Find Your Country/Region ▼

Terms of Use | Privacy | Cookie Policy | Accessibility | Site Map



© 2018 TE Connectivity. All Rights Reserved.