



Part Number : [190130033](#)

Product Description : InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 12-10 AWG, Yellow Insulator, Carton

Series Number : 19013

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : C-2319



Documents and Resources

Drawings

[190130033 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-008-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Melamine per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19013
Description	InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 12-10 AWG, Yellow Insulator, Carton
Comments	Loose in Bag
Product Name	InsulKrimp
Type	Piggyback Connector
UPC	822350973830

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V AC
-------------------	---------

Physical

Barrel Type	Closed - Brazed
Color - Resin	Yellow

Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.705/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	105°C
Wire Insulation Diameter	7.03mm max.
Wire Size (AWG)	10, 12

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640016200</u>

This document was generated on Apr 23, 2026