2011 Series

Pin Header 2.54mmX2.54mm(0.100"X0.100")



Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.
Contacts: Copper Alloy.

Electrical Characteristics:

Current Rating: 2 A.
Dielectric Withstanding Voltage: AC 1000V.
Insulator Resistance: 1000MΩ min.
Contact Resistance: 20mΩ max.
Operating Temperature: -40°C~+105°C.

Features:

* Available in Straight , Right Angle and Press Fit
* Side-to-side and end-to-end stackable.
* Custom design offered.
* Additional plating options available.

Mates with: 1001,2006,2041,2042,2043,2044,2045
2046,2047,2048,2049.





Dip Type



Press Fit Type



P.C. Board Layout

Position Dimension	4 Thru 80
A	2.54 X No. of Positions /2−0.25
B	2.54 X No. of Positions /2−2.54

Ordering information

2011-	2	X	40	G	00	S	P	B
Series	Double Row		No. of Pin Per Row	G: Gold Plated	00: G/F	S: Straight R: Right Angle	Blank: Dip Type P: Press Fit Type	B: Bulk Package

Custom Design: Straight (i.e. 2011-2 X 40 G00S-L1-L2); Right Angle (i.e. 2011-2 X 40 G00R-L1-L2-L3).
L1: Dip Length; L2: Mating Length; L3: Extended Length (currently only 1.42mm available.).
* Consult factory for Right Angle press fit drawing.

Information including designs, specifications and components may be changed or updated without notice.

Downloaded from Arrow.com.