

**Part Number :** 1301020117

**Product Description :** Super-Safeway Rubber Hand Lamp with 100W, Screw Release Guard with Reflector, with Switch and Side Outlet, Cord Length 7.62m (25.0'), Cord Type 16/3 SOOW

**Series Number :** 130102

**Status :** Active

**Product Category :** Lamps and Lights

**Engineering Number :** 106USA163



## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant                                     |
| China RoHS         | Not Relevant                                     |
| EU ELV             | Not Relevant                                     |
| Low-Halogen Status | Not Relevant                                     |
| REACH SVHC         | Not Reviewed per D(2023)3788-DC<br>(14 Jun 2023) |
| EU RoHS            | Not Relevant                                     |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

|        |        |
|--------|--------|
| Status | Active |
|--------|--------|

|                    |   |
|--------------------|---|
| Category           | Lamps and Lights  |
| Series             | 130102  |
| Description        | Super-Safeway Rubber Hand Lamp with 100W, Screw Release Guard with Reflector, with Switch and Side Outlet, Cord Length 7.62m (25.0'), Cord Type 16/3 SOOW |
| NEMA Configuration | NEMA 5-15   |
| Product Family     | Hand Lamps  |
| Product Name       | Super-Safeway   |
| Type               | Hand Lamps  |
| UPC                | 78678879471   |

## Electrical

|                             |      |
|-----------------------------|------|
| Lamp Wattage - Maximum      | 100W |
| Lumens                      | 1000 |
| On/Off Switch               | Yes  |
| Voltage (Fixture) - Maximum | 240V |

## Physical

|                         |                            |
|-------------------------|----------------------------|
| Bulb Type               | Incandescent               |
| Cord Length - Primary   | 7.62m (25.0')              |
| Cord Length - Secondary | N/A                        |
| Cord Type - Primary     | 16/3 SOOW                  |
| Depth                   | 101.60mm (4.000")          |
| Duty                    | Industrial                 |
| Guard Included          | Yes                        |
| Guard Type              | Reflector, Screw Release   |
| Height                  | 374.65mm (14.750")         |
| Lamp Type               | A21                        |
| Length                  | N/A                        |
| Material - Guard        | #8 Gauge Zinc-plated Steel |
| Mounting Style          | Hand Held                  |
| Net Weight              | 2179.055/g                 |
| Outlet                  | Side                       |
| Packaging Type          | Carton                     |

---

---

This document was generated on Sep 11, 2023