

- Find by
- Feature
- Browse by Category
- Browse by Application
- Shore

Search →

Enter part number or keyword

- Search Results (0)
- Search Options

No Search Results

Select a product type to narrow your search:

Connector

▼

Results with your selections: --

Family

- ◀

▶
- ☐ 0.64
- ☐ 040
- ☐ 070
- ☐ 56
- ☐ 59
- ☐ 090
- ☐ 187
- ☐ ACT
- ☐ ATS
- ☐ Apex
- ☐ BTS
- ☐ Bus-Bar
- ☐ CTS
- ☐ Coax
- ☐ DCK
- ☐ DCS-1
- ☐ DCS-2
- ☐ DS
- ☐ DSQ
- ☐ Ducon
- ☐ DuoTwin
- ☐ Fakra
- ☐ Flexible Power
- ☐ Fuse
- ☐ GT
- ☐ GT Flex Beam
- ☐ GTS
- ☐ GTS-2
- ☐ GTS-3
- ☐ HES
- ☐ HPCS
- ☐ HVISO
- ☐ High Power
- ☐ High Voltage
- ☐ Hyllok
- ☐ IDC
- ☐ Lamp Socket
- ☐ MCS
- ☐ MTS
- ☐ MTS-B
- ☐ Metri-Pack
- ☐ Micro
- ☐ Micro HVT
- ☐ Micro-Pack
- ☐ Mixed
- ☐ Modupack
- ☐ OCS
- ☐ Pack-Con III
- ☐ Performance Pack
- ☐ Power Pack
- ☐ RCS800
- ☐ RCS890
- ☐ Shield-Pack
- ☐ Sicma
- ☐ Sleeve
- ☐ Sleeve / Pin
- ☐ Squib / Interface-ABX UC
- ☐ Squib / Interface-ABX-3
- ☐ Squib / Interface-AK-1
- ☐ Squib / Interface-AK-2
- ☐ Squib / Interface-AK-2+
- ☐ Squib / Interface-FCI
- ☐ TTS
- ☐ Timer
- ☐ UC
- ☐ USB 2.0
- ☐ USCAR
- ☐ VF
- ☐ Weather Pack
- ☐ ZRT

▶

◀

Search →

Clear

Cavities

- ◀

▶
- ☐ 1
- ☐ 2
- ☐ 3
- ☐ 4
- ☐ 5
- ☐ 6
- ☐ 7
- ☐ 8
- ☐ 9
- ☐ 10
- ☐ 11
- ☐ 12
- ☐ 13
- ☐ 14
- ☐ 15
- ☐ 16
- ☐ 17
- ☐ 18
- ☐ 19
- ☐ 20
- ☐ 21
- ☐ 22
- ☐ 23
- ☐ 24
- ☐ 25
- ☐ 26
- ☐ 27
- ☐ 28
- ☐ 29
- ☐ 30
- ☐ 31
- ☐ 32
- ☐ 34
- ☐ 35
- ☐ 36
- ☐ 37
- ☐ 38
- ☐ 39
- ☐ 40
- ☐ 41
- ☐ 42
- ☐ 44
- ☐ 45
- ☐ 46
- ☐ 47
- ☐ 48
- ☐ 49
- ☐ 50
- ☐ 52
- ☐ 54
- ☐ 55
- ☐ 56
- ☐ 57
- ☐ 58
- ☐ 59
- ☐ 60
- ☐ 62
- ☐ 63
- ☐ 64
- ☐ 65
- ☐ 66
- ☐ 68
- ☐ 72
- ☐ 73
- ☐ 74
- ☐ 76
- ☐ 78
- ☐ 80
- ☐ 81
- ☐ 82
- ☐ 84
- ☐ 90
- ☐ 94
- ☐ 96
- ☐ 100
- ☐ 108
- ☐ 112
- ☐ 116
- ☐ 120
- ☐ 130
- ☐ 133
- ☐ 154
- ☐ 162
- ☐ 169
- ☐ 202

▶

◀

Search →

Clear

Gender

- ◀

▶
- ☐ Female
- ☐ Male

Search →

Clear

Sealed

- ◀

▶
- ☐ Sealed
- ☐ Unsealed

Search →

Clear

Terminal(s) blade size [mm]

☐ Mixed - Results will have exactly your selections in the same connector.

- ◀

▶
- ☐ 0.50
- ☐ 0.64
- ☐ 0.8
- ☐ 1.0
- ☐ 1.2
- ☐ 1.5
- ☐ 1.6 (round)
- ☐ 1.8
- ☐ 2.0 (round)
- ☐ 2.3
- ☐ 2.5
- ☐ 2.6
- ☐ 2.8
- ☐ 4.1
- ☐ 4.8
- ☐ 5.7
- ☐ 6.3
- ☐ 8.0
- ☐ 9.5
- ☐ 10.0
- ☐ 20.0

▶

◀

Search →

Clear

Product Segment

- ◀

▶
- ☐ Headers
- ☐ High Power
- ☐ Safety Restraint Systems (SRS)
- ☐ Standard Automotive

Search →

Clear

Application

- ◀

▶
- ☐ A/C Compressor
- ☐ Actuator
- ☐ Aerial / Antenna
- ☐ Airbag
- ☐ Alternator
- ☐ Antenna - Keyless System
- ☐ CAN
- ☐ Camera
- ☐ Cigar Lighter / Power Outlet
- ☐ Diagnostic
- ☐ Door To Body
- ☐ Electrovalve - Cold Start
- ☐ Fan - Engine Cooling
- ☐ Harness - Roof
- ☐ Heater - Rear Window
- ☐ Horn
- ☐ Ignition Coil
- ☐ Immobilizer
- ☐ Injector
- ☐ Inliner
- ☐ Instrument Cluster
- ☐ Lamp - Interior Lamp
- ☐ Lamp - Socket
- ☐ Latch
- ☐ Mirror
- ☐ Module - ABS
- ☐ Module - Airbag
- ☐ Module - Engine
- ☐ Module - Exterior
- ☐ Module - Interior
- ☐ Module - Transmission
- ☐ Motor - Blower
- ☐ Motor - Seat
- ☐ Motor - Wiper
- ☐ Multimedia
- ☐ Pad - Heated Seat
- ☐ Pump
- ☐ Relay
- ☐ Sensor - Accessories
- ☐ Sensor - Brakes
- ☐ Sensor - Crash
- ☐ Sensor - Engine
- ☐ Sensor - Exhaust
- ☐ Sensor - Exterior
- ☐ Sensor - Interior
- ☐ Sensor - Transmission
- ☐ Socket - Multimedia
- ☐ Socket - Tow Bar
- ☐ Speaker
- ☐ Starter
- ☐ Switch
- ☐ Switch - Multifunction

▶

◀

Search →

Clear

Clear

Search →

LOCK INRCONNECT CAV MDL 10

BLK

Part #13543542



Question about this product?

- Attributes
- Documents (3)
- Related Products (6)

Part # :	13543542
Description :	LOCK INRCONNECT CAV MDL 10 BLK
Product Type :	Connector
Status :	Active
Terminal(s) blade size	0.64
[mm] :	Unsealed
Sealed :	Female
Gender :	-40 to 85
Temperature range [°C] :	PBT
Material [g] :	0.82
Weight [g] :	Black
Color :	Yes
ELV compliant :	Yes
RoHS compliant :	Yes
Application :	Module - Door

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.

Follow Us

