



Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Input/Output (Box to Box) > Product Feature Selector > Product Details

2227225-2 Product Details

Share Print Email

Pluggable Connectors, Cages & Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- zQSFP+ Product Line
- Cage Assembly with Integrated Connector
- zQSFP+ Application
- Connector Style = Receptacle
- Cage Type = Stacked

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 2227225-2

Preliminary

View 3D PDF

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Feedback

Documentation & Additional Information	
Product Drawings: • CAGE AND CONNECTOR ASSEMBLY, WITH EMI GASKET, 2X2, Z... (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version 1) • 3D Model (IGES, Version 1) • 3D Model (STEP, Version 1)	Related Products: • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Line = zQSFP+ • Product Type = Cage Assembly with Integrated Connector Mechanical Attachment: • PCB Mount = Single Sided • Bezel Mounting Style = Behind Bezel Electrical Characteristics: • Data Signal Rate (Gb/s) = Up to 100 Termination Features: • Termination Method to PC Board = Through Hole - Press Fit Dimensions: • Tail Length (mm [in]) = 2.7 [0.1063] • PCB Thickness, Recommended (mm [in]) = 1.57 [0.062] • Length (X-Axis) (mm [in]) = 73.16 [2.880] • Width (Z-Axis) (mm [in]) = 43.05 [1.695] • Profile Height (Y-Axis) (mm [in]) = 29.59 [1.165] Body Features: • Integrated Light Pipes = Yes Contact Features: • Contact Plating, Mating Area, Material = Gold • Tail Plating Material = Gold • Contact Base Material = Copper Alloy • Contact Plating, Mating Area, Thickness (µm [µin]) = 0.76 [29.92] • Underplate Material = Nickel Silver Alloy	Housing Features: • Connector Style = Receptacle • Cage Type = Stacked Configuration Features: • Port Configuration = 2x2 • Lightpipe = With • Lightpipe Configuration = Outer, Left Indicator Up • EMI Containment = Elastomeric Gasket, EMI Springs Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: • Applies To = Printed Circuit Board Operation/Application: • Application = zQSFP+ • Heat Sink Application = No Other: • Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

