
Your Expert Partner for **Human Machine Interfaces**

# Actuator

704.411.0



https://www.eao.com/component/704.411.0/en/ac...

Downloaded from Arrow.com.

Your product:



# 704.411.0
# Actuator

## FRONT

| | |
|---|---|
| **Front dimension:** | Ø 29 mm |
| **Front form:** | Round |
| **Front bezel colour:** | Nature |
| **Front bezel material:** | Aluminium |

## MOUNTING

| | |
|---|---|
| **Design:** | Raised |
| **Mounting cut-out:** | Ø 22.5 mm |
| **Mounting type:** | Panel mounting |

## OPERATING-/INDICATION PART

| | |
|---|---|
| **Lever colour:** | Black |
| **Lever bar colour:** | White |
| **Lever material:** | plastic |
| **Lever shape:** | short |

## ELECTRICAL CHARACTERISTICS

| | |
|---|---|
| **Standards:** | The switches comply with the “Standards for low-voltage switching devices” DIN EN 60947-1 |

## MECHANICAL CHARACTERISTICS

| | |
|---|---|
| **Switching action:** | Rest - Maintained |
| **Switching positions:** | 2 positions |

Downloaded from Arrow.com.

| | |
|---|---|
| **Switching angle:** | 90° right / -45° ... +45° |
| **Mechanical lifetime:** | ≤2.5 Mil. cycles of operation |
| **Weight:** | 0.032 kg |


## AMBIENT CONDITION

| | |
|---|---|
| **IP Protection:** | IP65 front side |
| **Operating temperature:** | – 40 °C ... + 55 °C |
| **Storage temperature:** | – 40 °C ... + 85 °C |


## CERTIFICATE

| | |
|---|---|
| **REACH:** | REACH compliant |
| **RoHS:** | RoHS compliant |

## OTHER


| | |
|---|---|
| **Short Description:** | Actuator, Ø 22.5 mm, Ø 29 mm, non illuminative, Black, short, Round, Nature, Aluminium, anodised, Rest - Maintained |
| **Hints:** | Max. 3 switching elements can be clipped on |
| **max. number of switching elements:** | 3 |
| **Switching positions:** |   |
| **Wiring diagrams:** |  |
| **Mounting cut-outs:** | |

Downloaded from Arrow.com.




A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

**Dimension drawings:**




A = Screw terminal

Downloaded from Arrow.com.