



Part Number : [2157112114](#)

Product Description : Pre-Crimped Lead Clik-Mate Male-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Red

Series Number : 215711

Status : Active

Product Category : Power and Signal Cable Assemblies


Documents and Resources

Drawings

[2157112114 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215711
Description	Pre-Crimped Lead Clik-Mate Male-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Red
Application	Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	CLIK-Mate Terminal-to-Pigtail
Keyword	Pre-Crimped Leads
Product Name	CLIK-Mate
UPC	193264605293

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Male-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.714/g
Packaging Type	Bag

Plating min - Mating	0.406µm
Plating min - Termination	0.406µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	26

Mates With / Use With

Use with Part(s)

Description	Part Number
1.50mm Pitch CLIK-Mate Single Row Plug Housings	<u>502578</u>
1.50mm Pitch CLIK-Mate Dual Row Plug Housings	<u>503149</u>

This document was generated on Jun 04, 2026