Marshalling panel - PTRV 4 /GY - 3270117



Marshalling panel, nom. voltage: 250 V, nominal current: 10 A, cross section: 0.14 mm² - 2.5 mm², AWG: 14 - 26, connection method: Push-in connection, number of positions: 2, number of connections: 16, width: 8.3 mm, length: 64 mm, color: gray, color of connection elements: gray, mounting: NS 35/7,5, NS 35/15

Generate product PDF

PHOENIX CONTACT

586 Fulling Mill Road
Middletown, PA 17057

(800) 888-7388

Ask a question

Find product experts

Available

Add to product comparison | Add to part list | Find a distributor | Add to wish list

Overview | Technical data | Accessories | Approvals | Downloads

Your advantages

- High contact quality thanks to push-in technology as a replacement for Wire-Wrap®, TERMI-POINT®, etc.
- Tool-free wiring in a confined space thanks to compact size
- Individual color assignment of cable and terminal point to ensure error-free, safe operation
- The 2.3 mm test connection enables testing between the conductors with test pins commonly used in the industry

RoHS

COMPLETE line

Key Commercial Data

Orderkey	3270117
Packing unit	1 pc
Minimum order quantity	10 pc
Catalog page	Page 46 (C-1-2019)
GTIN	4055626435176
Weight per Piece (excluding packing)	18.000 g
Custom tariff number	85369010
Country of origin	PL (Poland)

© 2020 PHOENIX CONTACT Terms and Conditions Privacy Policy Sitemap

Downloaded from Arrow.com.