

Cable Sealing thermop PG21 18-14mm black



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5157
Specification	Cable Sealing thermop PG21 18-14mm black
HARTING eCatalogue	https://harting.com/09000005157

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods for cable to cable housing

Technical characteristics

Tightening torque	≤8 Nm (depending on the cable and the seal insert used)
Wrench size	33
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65
Size	Pg 21
Clamping range	14 ... 18 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	10
Net weight	12.4 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140001985
eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431