

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430017

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 14 Gauge SOOW with Lock Blade, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA L7-15, 277V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

IP67

NEMA Configuration

NEMA L7-15

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Type

Cordset

UPC

78678807736

Physical

Cord Grip Body Size

F2 1/2"

Flange

No

Flip Lid

No

Gender

Male-Female

Length

7.62m (25.0')

Locking Blade

Yes

Net Weight

333.000/g

Poles

2-pole/3-wire

Electrical

Cord Type

12/3 SOOW

Current - Maximum per Contact

15.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

277V

Material Info

Engineering Number

24W34A163

Reference - Drawing Numbers

Sales Drawing

1301430185-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION