



Search

Amphenol Part # [Find](#)

Cross Reference # [Find](#)

Locate Inventory [Find](#)

RSE112117

Series:	MIL-PRF-12883
Type:	Low Profile
Number of Poles:	3
Number of Contacts:	11
Number of Contacts per Size:	9, 2
Contact Size:	12, 16
Contact Part Number:	M39029/92-533
With or Without Hardware:	Available upon request
With or Without Contacts:	With
Configuration:	N/A
Amperage:	Available upon request
Mounting Stud:	Fixed
QPL:	N/A
Mil-Spec:	Available upon request
Temperature (Degrees C):	-65 to 125
Insulation Resistance:	1000 Megaohms Min.
Dielectric Withstanding Voltage:	1500 VRMS at Sea Level; 700 VRMS at 80,000 ft.
Vibration:	MIL-STD-202, Method 204 Test Condition G
Shock:	MIL-STD-202, Method 213 Test Condition C
Body:	Polyetherimide per ASTM-D5205
Grommet:	Silicone Rubber per A-A-59588
Hardware Material:	Stainless Steel or Steel with Cadmium Chromate Finish
Contact Retainers:	Beryllium Copper
Removable Socket Contacts:	Copper Alloy, Hard Gold Plated in Accordance with MIL-G-45204
Engineering PDF:	RSE112115_C.pdf

