

PRODUCT SELECTOR

PRODUCT TYPE	POSITIONS	IP RATING	AMPERAGE	HOUSING MATERIAL	PRODUCT LINE
Search All ▼	Search All ▼	Search All ▼	Search All ▼	Search All ▼	Search All ▼

VOLTAGE

Search All ▼	RESET	SEARCH
------------------------------	-------	--------

Home > Market Applications > Heavy Equipment > Agriculture > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS > RT061619SNHEC03 Plug, Female, with Silicone O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192993-0054



RT061619SNHEC03 PLUG, FEMALE, WITH SILICONE O-RING SEAL AND END CAP WITH INDIVIDUAL REAR WIRE SEAL, 19 CONTACTS, SIZE 16, 14-26AWG, 13A/300V, SHELL SIZE 16. COMPATIBLE TO PART # 192993-0054

PART NUMBER: RT061619SNHEC03

[DATASHEET](#) [View / Download](#)

SPECIFICATIONS:

Male/Female: Female
Shell Size: 16
Number of Contacts: 19
Contact Pin/Socket: Socket
Contact Size: 16
Contact Type: O-Ring Seal
AWG: 14-26
Amperage: 13
Voltage: 300
IP Rating: IP67
Insulation Diameter (OD) Min-Max: Ø2.0mm - Ø3.2mm
Salt Spray: 48 H
Mating Parts: RT001619PNH*, RT071619PNH* Receptacles

QUANTITY

1	REQUEST A QUOTE
---	-----------------

Like Sign Up to see what your friends like.

Like Sign Up to see what your friends like.

DESCRIPTION

Plug, Female, with Silicone O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part #

RELATED ITEMS



RT016DC Receptacle Dustcap without Chain, Shell Size 16. Compatible to part # UT016DC



RT016DCG Receptacle Dustcap with Chain, Shell Size 16. Compatible to part # UT016DCG



RT016RL Receptacle Dustcap with Nylon Cord, Made of Rubber, Shell Size 16



RT001619PNH Square Flange Receptacle, Male, 19 Contacts, 14-26AWG, 13A/250V, Shell Size 16. Compatible to part # UT001619PH, 192990-1790, G2B1619PN



RT001619PNHEC Square Flange Receptacle, Male, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192900-0078



RT001619PNHK Square Flange Receptacle Kit, Male, IP67. Including Receptacle, Gasket & Contacts, 19 Contacts, 18-16AWG, 13A/300V, Shell Size 16. Compatible to part # UT001619PH



RT001619SNH Square Flange Receptacle, Female, 19 Contacts, 14-26AWG, 13A/250V, Shell Size 16. Compatible to part # UT001619SH, 192990-1690, G2B1492SN



RT001619SNHEC Square Flange Receptacle, Female, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192900-0039



RT001619SNH-K Square Flange Receptacle Kit, Female, IP67. Including Receptacle, Gasket &



108039116 Locking Clip with Lanyard, Shell Size 16



CA-4016-59 Sealing Plug, Size 16-



RB00011916 Receptacle Dustcap without Nylon Cord, Rubber Material, Shell Size 16

Contacts, 19 Contacts, 18-16AWG,
13A/300V, Shell Size 16. Compatible
to part # UT001619SH



MFX-3954 Hand Tool, Stamped &
Formed Contact, Size 16, 20-14AWG



MFX-3957 Crimp Die for Stamped &
Formed Contact



QXRT16 Contact Extraction Tool,
#16 (Ø 1.6) Contact. Compatible to
part # RX2025GE1



MFX-3959 Hand Crimp Tool for
Machined Contact



MFX-3960 Pneumatic Crimp Tool for
Machined Contacts



MP14M23F Pin Contact, Machined,
Size 16, Gold Flash, Wire Range 2.0-
2.5mm², 14AWG. Compatible to
part # RM14M30J



MP14M23G10 Pin Contact,
Machined, Size 16, Gold 10µ", Wire
Range 2.0-2.5mm², 14AWG



MP14M23G15 Pin Contact, Machined,
Size 16, Gold 15µ", Wire Range 2.0-
2.5mm², 14AWG



MP14M23G30 Pin Contact, Machined,
Size 16, Gold 30µ", Wire Range 2.0-
2.5mm², 14AWG



MP14M23G5 Pin Contact,
Machined, Size 16, Gold 5µ", Wire
Range 2.0-2.5mm², 14AWG



MP16M23G15 Pin Contact, Size 16,
Machined, Gold 15µ", Wire Range
.75-1.5mm², 18-16 AWG



MP16M23G30 Pin Contact, Size 16,
Machined, Gold 30µ", Wire Range
.75-1.5mm², 18-16 AWG. Compatible
to part # RM16M23N, 192991-0085



MP16M23G5 Pin Contact, Size 16, Machined, Gold 5µm, Wire Range .75-1.5mm², 18-16 AWG



MP20M23F Pin Contact, Machined, Size 16, Gold Flash, Wire Range .34-.50mm², 22-20 AWG. Compatible to part # RM20M13J, 192991-0095, 192991-0127



MP24M23F Pin Contact, Machined, Size 16, Gold Flash, Wire Range .14-.25mm², 24-26 AWG. Compatible to part # RM24M23J, 192991-0091



MP16M23F Pin Contact, Size 16, Machined, Gold Flash, Wire Range .75-1.5mm², 18-16 AWG. Compatible to part # RM16M23J, 192991-0083



MP16M23G10 Pin Contact, Size 16, Machined, Gold 10µm, Wire Range .75-1.5mm², 18-16 AWG



MP20M23G10 Pin Contact, Machined, Size 16, Gold 10µm, Wire Range .34-.50mm², 22-20 AWG



MP20M23G15 Pin Contact, Machined, Size 16, Gold 15µm, Wire Range .34-.50mm², 22-20 AWG



MP20M23G30 Pin Contact, Machined, Size 16, Gold 30µm, Wire Range .34-.50mm², 22-20 AWG. Compatible to part # RM20M23N, 192991-0097, 192991-0128



MP20M23G5 Pin Contact, Machined, Gold 5µm, Wire Range .34-.50mm², 22-20 AWG



MP24M23G10 Pin Contact, Machined, Size 16, Gold 10µm, Wire Range .14-.25mm², 26-24 AWG



MP24M23G15 Pin Contact, Machined, Size 16, Gold 15µm, Wire Range .14-.25mm², 26-24 AWG



MP24M23G30 Pin Contact, Machined, Size 16, Gold 30µm, Wire Range .14-.25mm², 26-24 AWG. Compatible to part # RM24M23N, 192991-0093



MP24M23G5 Pin Contact, Machined,
Size 16, Gold 5 μ ", Wire
Range .14-.25mm², 26-24 AWG



MS14M23F Socket Contact,
Machined, Size 16, Gold Flash, Wire
Range 2.0-2.5mm², 14AWG.
Compatible to part # RC14M30J



MS14M23G10 Socket Contact,
Machined, Size 16, Gold 10 μ ", Wire
Range 2.0-2.5mm², 14AWG



MS14M23G15 Socket Contact,
Machined, Size 16, Gold 15 μ ", Wire
Range 2.0-2.5mm², 14AWG



MS14M23G30 Socket Contact,
Machined, Size 16, Gold 30 μ ", Wire
Range 2.0-2.5mm², 14AWG



MS14M23G5 Socket Contact,
Machined, Size 16, Gold 5 μ ", Wire
Range 2.0-2.5mm², 14AWG



MS16M23G5 Socket Contact, Size
16, Machined, Gold 5 μ ", Wire Range
.75-1.5mm², 18-16 AWG



MS20M23F Socket Contact,
Machined, Size 16, Gold Flash, Wire
Range .34-.50mm², 20-22 AWG.
Compatible to part # RC20M13J,
192991-0038,192991-0039



MS20M23G10 Socket Contact,
Machined, Size 16, Gold 30 μ ", Wire
Range .34-.50mm², 22-20 AWG



MS20M23G15 Socket Contact,
Machined, Size 16, Gold 30 μ ", Wire
Range .34-.50mm², 22-20 AWG



MS16M23F Socket Contact, Size 16,
Machined, Gold Flash, Wire Range
.75-1.5mm² 16-18 AWG. Compatible
to part # RC16M23J, 192991-0041



MS16M23G10 Socket Contact, Size
16, Machined, Gold 10 μ ", Wire Range
.75-1.5mm², 18-16 AWG



MS16M23G15 Socket Contact, Size
16, Machined, Gold 15 μ ", Wire Range
.75-1.5mm², 18-16 AWG

MS16M23G30 Socket Contact, Size
16, Machined, Gold 30 μ ", Wire
Range .75-1.5mm², 18-16 AWG,
Compatible to part # RC16M23N,
192991-0059

MS20M23G30 Socket Contact,
Machined, Size 16, Gold 30 μ ", Wire
Range .34-.50mm², 22-20 AWG.
Compatible to part #RC20M23N,
192990-0056,192991-0057

MS20M23G5 Socket Contact,
Machined, Size 16, Gold 5 μ ", Wire
Range .34-.50mm², 22-20 AWG



RT061619PNH Plug, Male, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # UT061619PH, 192922-1280, G6B1619PN



RT061619PNH03 Plug, Male with Silicone Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # UT061619PH



RT061619PNHEC Plug, Male with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192900-0017



RT061619PNHEC03 Plug, Male, with Silicone O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192993-0014



RT061619PNH-K Plug Kit, Male, IP67. Including Connector, Backshell & Contacts, 19 Contacts, Size 16, 18-16AWG, 13A/300V, Shell Size 16. Compatible to part # UT061619PH



RT061619SNH Plug, Female, 19 Contacts, Size 16, 14-26AWG, 13A/250V, Shell Size 16. Compatible to part # UT061619SH, 192926-0530, G6B1619SN



RT061619SNH03 Plug, Female with Silicone Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # UT061619SH



RT061619SNHEC Plug, Female, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192900-0057



RT061619SNH-K Plug Kit, Female, IP67. Including Connector, Backshell & Contacts, 19 Contacts, Size 16, 18-16AWG, 13A/300V, Shell Size 16. Compatible to part # UT061619SH



RT071619PNHEC Jam Nut Receptacle, Male, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Contact Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192900-0353



RT071619PNHEC03 Jam Nut Receptacle, Male with Silicone O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Contact Size 16, 14-26AWG, 13A/300V, Shell Size 16



RT071619PNH-K Jam Nut Receptacle Kit, Male, IP67. Including Receptacle & Contacts, 19 Contacts, Contact Size 16, 18-16AWG, 13A/300V, Shell Size 16. Compatible to part # UT071619PH



RT071619SNH Jam Nut Receptacle, Female, 19 Contacts, Contact Size 16, 14-26AWG, 13A/250V, Shell Size 16. Compatible to part # UT071619SH, G4B1619SN

RT071619SNH03 Jam Nut Receptacle, Female with Silicone Seal, 19 Contacts, Contact Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # UT071619SH

RT071619SNHEC Jam Nut Receptacle, Female, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Contact Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192900-0490

RT071619SNHEC03 Jam Nut Receptacle, Female with Silicone O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, Contact Size 16, 14-26AWG, 13A/300V, Shell Size 16



RT071619SNH-K Jam Nut Receptacle, Female, IP67. Including Receptacle & Contacts, 19 Contacts, Contact Size 16, 18-16AWG, 13A/300V, Shell Size 16. Compatible to part # UT071619SH

SS14M1G10 Socket Contact, Stamped, Size 16, Gold 10μ", Wire Range 2.0-2.5mm², 14AWG, 13A

SS14M1G15 Socket Contact, Stamped, Size 16, Gold 15μ", Wire Range 2.0-2.5mm², 14AWG, 13A

SS14M1G30 Socket Contact, Stamped, Size 16, Gold 30μ", Wire Range 2.0-2.5mm², 14AWG, 13A



SS14M1G5 Socket Contact, Stamped, Size 16, Gold 5μ", Wire Range 2.0-2.5mm², 14AWG, 13A

SS16M1F Socket Contact, Stamped, Size 16, Gold Flash, Wire Range .75-1.5mm², 18-16AWG, 13A. Compatible to part # SC16M11D70, 192990-2670

SS16M1G10 Socket Contact, Contact, Size 16, Stamped, 10μ", Wire Range .75-1.5mm², 18-16AWG, 13A

SS16M1G15 Socket Contact, Size 16, Stamped, Gold 15μ", Wire Range .75-1.5mm², 18-16AWG, 13A



SS16M1G30 Socket Contact, Stamped, Size 16, Gold 30μ", Wire Range .75-1.5mm², 18-16AWG, 13A



SS16M1G5 Socket Contact, Stamped, Size 16, Gold 5μ", Wire Range .75-1.5mm², 18-16AWG, 13A



SS20M1F Socket Contact, Size 16, Stamped, Gold Flash, Wire Range .34-.50mm², 20-22AWG, 13A. Compatible to part # SC20M1D70, 192990-2680



SS20M1G10 Socket Contact, Size 16, Stamped, Gold 10μ", Wire Range .34-.50mm², 22-20AWG, 13A



SS20M1G15 Socket Contact, Stamped, Size 16, Gold 15μ", Wire Range .34-.50mm², 22-20AWG, 13A

RT071619PNH Jam Nut Receptacle, Male, 19 Contacts, Contact Size 16, 14-26AWG, 13A/250V, Shell Size 16. Compatible to part # UT071619PH, G4B1619PN

RT071619PNH03 Jam Nut Receptacle, Male with Silicone Seal, 19 Contacts, Contact Size 16, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # UT071619PH

RT0B-16CG-NS1 Backshell (90°), Cable Range 10.0-14.0mm



RT0B-16CG-NS2 Backshell (90°), Cable Range 13.5-17.0

RT0L-16CG-S1 Long Backshell (straight), Cable Range 9.0-14.5mm

RT0L-16CG-S2 Long Backshell (straight), Cable Range 13.5-17.0mm

RT0S-16CG-NS1 Short Backshell (straight), Cable Range 9.0-14.5mm



RT0S-16CG-NS2 Short Backshell (straight), Cable Range 13.5-17.0mm

RT616DC Plug Dustcap without Chain, Shell Size 16. Compatible to part # UTG616DC

RT616DCG Plug Dustcap with Chain, Shell Size 16. Compatible to part # UTG616DCG

RTFD16B Square Flange Receptacle Gaskets, Shell Size 16, Thickness 0.8mm (±0.2). Compatible to part # UTFD15B



SP14M1F Pin Contact, Stamped, Size 16, Gold Flash, Wire Range 2.0-2.5mm², 14AWG, 13A. Compatible to part # SM14M1D70, 192990-2620



SP14M1G10 Pin Contact, Stamped, Size 16, Gold 10µ", Wire Range 2.0-2.5mm², 14AWG, 13A



SP14M1G15 Pin Contact, Stamped, Size 16, Gold 15µ", Wire Range 2.0-2.5mm², 14AWG, 13A



SP14M1G30 Pin Contact, Stamped, Size 16, Gold 30µ", Wire Range 2.0-2.5mm², 14AWG, 13A



SP14M1G5 Pin Contact, Stamped, Size 16, Gold 5µ", Wire Range 2.0-2.5mm², 14AWG, 13A



SP16M1F Pin Contact, Stamped, Size 16, Gold Flash, Wire Range .75-1.5mm², 18-16AWG, 13A. Compatible to part # SM16M11D70, 192990-2630



SP16M1G10 Pin Contact, Stamped, Size 16, Gold 10µ", Wire Range .75-1.5mm², 18-16AWG, 13A



SP16M1G15 Pin Contact, Stamped, Size 16, Gold 15µ", Wire Range .75-1.5mm², 18-16AWG, 13A



SP16M1G30 Pin Contact, Stamped, Size 16, Gold 30µ", Wire Range .75-1.5mm², 18-16AWG, 13A



SP16M1G5 Pin Contact, Stamped, Size 16, Gold 5µ", Wire Range .75-1.5mm², 18-16AWG, 13A



SP20M1F Pin Contact, Stamped, Size 16, Gold Flash, Wire Range .34-.50mm², 22-20AWG, 13A. Compatible to part # SM20M1D70, 192990-2640



SP20M1G10 Pin Contact, Stamped, Size 16, Gold 10µ", Wire Range .34-.50mm², 22-20AWG, 13A



SP20M1G15 Pin Contact, Stamped, Size 16, Gold 15μ", Wire Range .34-.50mm², 22-20AWG, 13A



SP20M1G30 Pin Contact, Stamped, Size 16, Gold 30μ", Wire Range .34-.50mm², 22-20AWG, 13A



SP20M1G5 Pin Contact, Size 16, Stamped, Gold 5μ", Wire Range .34-.50mm², 22-20AWG, 13A



SP24M1F Pin Contact, Stamped, Size 16, Gold Flash, Wire Range .14-.25mm², .14-.25mm², 26-24AWG, 13A. Compatible to part # SM24M1D70, 192990-2650



SP24M1G10 Pin Contact, Stamped, Size 16, Gold 10μ", Wire Range .14-.25mm², 26-24AWG, 13A



SP24M1G15 Pin Contact, Stamped, Size 16, Gold 15μ", Wire Range .14-.25mm², 26-24AWG, 13A



SP24M1G30 Pin Contact, Stamped, Size 16, Gold 30μ", Wire Range .14-.25mm², 26-24AWG, 13A



RT001619SNHEC03 Square Flange Receptacle, Female, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192993-0034



SP24M1G5 Pin Contact, Stamped, Size 16, Gold 5μ", Wire Range .14-.25mm², 26-24AWG, 13A



SS20M1G30 Socket Contact, Stamped, Size 16, Gold 30μ", Wire Range .34-.50mm², 22-20AWG, 13A



SS20M1G5 Socket Contact, Size 16, Stamped, Gold 5μ", Wire Range .34-.50mm², 22-20AWG, 13A



SS24M1G10 Socket Contact, Stamped, Size 16, Gold 10μ", Wire Range .14-.25mm², 26-24AWG, 13A



SS24M1G15 Socket Contact, Stamped, Size 16, Gold 15μ", Wire Range .14-.25mm², 26-24AWG, 13A

SS24M1G30 Socket Contact, Stamped, Size 16, Gold 30μ", Wire Range .14-.25mm², 26-24AWG, 13A

SS24M1G5 Socket Contact, Stamped, Size 16Gold 5μ", Wire Range .14-.25mm², 26-24AWG, 13A

SS14M1F Socket Contact, Stamped, Size 16, Gold Flash, Wire Range 2.0-2.5mm², 14 AWG, 13A. Compatible to part # SC14M1D70, 192990-2660



SS24M1F Socket Contact, Stamped, Size 16, Gold Flash, Wire Range .14-.25mm², 26-24AWG, 13A. Compatible to part # SC24M1D70, 192990-2690

RT001619PNHEC03 Square Flange Receptacle, Male, with O-ring Seal and End Cap with Individual Rear Wire Seal, 19 Contacts, 14-26AWG, 13A/300V, Shell Size 16. Compatible to part # 192993-0074

BROWSE SIMILAR ITEMS

- > Market Applications > Heavy Equipment > Construction > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Heavy Equipment > Transportation > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Heavy Equipment > Off Road Recreation > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Heavy Equipment > Mining > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Heavy Equipment > Industrial > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Our Product Lines > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Heavy Equipment > Railway > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Automation > Conveyors > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Automation > Packaging Machinery > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Automation > Motion Control / Servo Motors > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Automotive > Diagnostics > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Automotive > Hybrid Electric > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Water Resistant - Waterproof > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Harsh Environments > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Medical > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Renewable Energy > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > UV Market > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Lighting & Traffic Control > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS
- > Market Applications > Wireless Infrastructure > Ecomate Connectors > Ecomate RM > 19 Position 13A/300V > PLUGS

LINKS

- > Company
- > Contact
- > Privacy Policy
- > Terms and Conditions
- > Code of Business Conduct and Ethics
- > ISO Certification
- > Quality Policy
- > Industrial@Amphenol News
- > Test Reports

SHOP

- > Our Product Lines
- > Market Applications
- > Distributors

FOLLOW US!



