Part Number : 192030113
Product Description : Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : C-U-128-10



Documents and Resources

Drawings

192030113_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton
Comments	1200° F (649° C)
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	800755059533

Agency

UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Net Weight	1.326/g
Packaging Type	Carton
Stud Size	10 (M5)
Wire Size (AWG)	10, 12

Downloaded from Arrow.com.

Wire Size mm^2	4.00-6.00

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm^2 - 0.5mm^2	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on Apr 14, 2026

Downloaded from Arrow.com.