

Project: PTF Series
Status: Production
Date: August 9th 2013
Rev 1

PTF Series				
Characteristic	OPTF0075P / OPTF0075PXBL	OPTF0077P	OPTF0078P	
Fuse Link	5X20	5X20	5X20	
Mounting	PCB	PCB	PCB	
Rated Current	6.3 Amp.	6.3 Amp.	6.3 Amp.	
Rated Voltage	250 VAC	250 VAC	250 VAC	
Rated Power Acceptance	1.6 W	1.6 W	1.6 W	
Housing	PA UL-94 V0	PA UL-94 V0	PA UL-94 V0	
Admissible Air Temperature	-30° C to 85°C	-30° C to 85°C	-30° C to 85°C	
Schoksafe Catgory	PC1	PC1	PC1	
Degree of Protection	IP00	IP00	IP00	
Contact Resistance	< 5.0 mΩ	< 5.0 mΩ	< 5.0 mΩ	
VDE Rated Current	6.3 Amp.	6.3 Amp.	6.3 Amp.	
VDE Rated Voltage	250 VAC	250 VAC	250 VAC	
VDE Rated Power Acceptance	1.6 W	1.6 W	1.6 W	
UR Rated Current	10 Amp.	10 Amp.	10 Amp.	
UR Rated Voltage	250 VDC	250 VDC	250 VDC	
UR Rated Power Acceptance	-	-	-	

