





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		UPDATED DIM.	3/20/15	HR/L



SPECIFICATIONS:

Material:

Insulator: Nylon, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC/DC max

Current rating: AC/DC 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

ROHS
COMPLIANT

Positions: 2 thru 12
A = .156 [3.96] x No. of Positions + .008 [0.20]
B = .156 [3.96] x No. of Spaces

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.156 [3.96] POWER HEADER

RIGHT ANGLE, WITH REAR LOCK

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]				TOLERANCES: EXCEPT AS NOTED			
INCHES				HOLES			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS		4/12/05	TITLE	SIZE	PART NO.	REV.
CHECKED					X	LHC-XX-TRA	A
APPROVED				REF:	S0006T	SCALE: NTS	SHEET 1 OF 1