


.062" PITCH COMPLIANT PIN

HD Stacker™



GSTB (.095) single-sided mating connector Bottom-of-stack


MATES WITH GSTB AND GSTBL




- Innovative Chevron Contact System (CCS)
- High-density layouts from 40 to 300 contacts
- Polarized insulators
- Keyed guide pin hardware for mis-mate protection

How to Order GSTB (.095) HD Stackers					
Sample Part Number		GSTB	-120	-.095	-B 1
Series	GSTB = Standard Profile Stacker				
Number of Contacts	40, 80, 120, 160, 200, 240, 300				
Zero Termination Length	.095				
Hardware	B Keyed Guide Pins for bottom stack				
Key Position	1* PIN 1 R R 2 PIN 1 R L 3 PIN 1 L L 4 PIN 1 L R				


* Choose Hardware/Key Position -B1 for best availability / fastest delivery



All Glenair HD Stacker™ connectors are equipped with our innovative .062" pitch high-density Chevron Contact System (CCS). Special non-orthogonal socket tines enable both higher density layouts as well as improved signal integrity. The GSTB (.095) is equipped with socket contacts with solder-free press-fit board mounting section only (no pin contacts)



The GSTB (.095) is used in bottom-of-stack applications that only require a single-sided mating interface. Shown: GSTB (.095) on bottom, stack-mating with GSTB above.



Number of Contacts	A		B	
	in	mm	in	mm
40	0.90	22.86	0.70	17.78
80	1.40	35.56	1.20	30.48
120	1.90	48.26	1.70	43.18
160	2.40	60.96	2.20	55.88
200	2.90	73.66	2.70	68.58
240	3.40	86.36	3.20	81.28
300	4.15	105.41	3.95	100.33