

16GB, 32GB, 64GB, 128GB, 256GB, and 512GB*

SanDisk Ultra® USB 3.0 Flash Drive

Portability meets speed

Highlights

- Transfer up to 10x faster than USB 2.0[1]
- Backward compatible with USB 2.0
- Secure file encryption and password protection with included SanDisk SecureAccess™ software[3]
- Recover lost or corrupted files with a year's subscription to RescuePRO® software

With the high-speed SanDisk Ultra® USB 3.0 Flash Drive you can transfer up to ten times faster than standard USB 2.0 drives. Transfer a full-length movie in less than 40 seconds[2]—so you spend less time waiting, more doing.

You can generously share your favorite media while keeping your private files private with password protection through SanDisk SecureAccess™ software. Backward compatible with USB 2.0, this USB 3.0 flash drive comes with a five-year warranty.



SanDisk SecureAccess™



SanDisk®
a Western Digital brand

Downloaded from Arrow.com.

SanDisk Ultra® USB Flash Drive Specifications	
Performance	Up to 130MB/s read speed[1]
Dimensions	56.09 x 21.59 x 10.41mm or 2.87 x 0.87 x 0.42in.
Available capacities	16GB, 32GB, 64GB, 128GB, 256GB, and 512GB*
Operating temperature	32° – 113°F (0° – 45°C)
Storage temperature	50° – 158°F (–10° – 70°C)
USB port	USB 3.0 enabled (USB 2.0 compatible)
Software	SanDisk SecureAccess™ software[3]
	RescuePRO® file recovery software (one-year subscription offer)
Warranty	5-year limited warranty (U.S.); 5-year warranty (ROW)

For more information, please visit
www.sandisk.com

SanDisk®
a Western Digital brand

At SanDisk®, we're expanding the possibilities of data storage. For more than 25 years, SanDisk's ideas have helped transform the industry, delivering next generation storage solutions for consumers and businesses around the globe.

Western Digital Technologies, Inc.
951 SanDisk Drive | Milpitas | CA 95035 | USA

Western Digital Technologies, Inc. is the seller of record and licensee in the Americas of SanDisk® products.

* 1GB = 1,000,000,000 bytes. Actual user storage less.
[1] (**for 32GB, 64GB, 128GB, 256GB and 512GB***) Write to drive up to 10 times faster than standard USB 2.0 drives (4MB/s); up to 130MB/s read speed. USB 3.0 port required. Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes.
(**for 16GB**) Write to drive up to 5 times faster than standard USB 2.0 drives (4MB/s); up to 130MB/s read speed. USB 3.0 port required. Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes.
[2] Based on 1.2GB MPEG-4 video transfer with USB 3.0 host device. Results may vary based on host device, file attributes and other factors.
[3] Password protection uses 128-bit AES encryption and is supported by Windows® 7, Windows 8, Windows 10, and Mac OS X v10.9+ (Software download required for Mac, see www.SanDisk.com/SecureAccess).

SanDisk, the SanDisk logo, RescuePRO, SanDisk Secure Access, and SanDisk Ultra are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. Mac and Mac OS are trademarks of Apple, Inc. All other trademarks are the property of their respective owners.
©2020 Western Digital Corporation or its affiliates. All rights reserved. 01/20

Downloaded from Arrow.com.