

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0981721003

Status:

Active - Custom

Description:

5.00mm (.197") NSCC Wire-to-Wire 2.80mm (.110") Receptacle Housing, With TPA™, 6 Circuits, Gray

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Crimp Housings

Series

98172

Application

Power

Product Name

NSCC

Physical

Circuits (maximum)

6

Color - Resin

Black, Natural

Gender

Female

Glow-Wire Compliant

No

Lock to Mating Part

Yes

Material - Resin

Polyester

Number of Rows

2

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

5.00mm (.197")

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Electrical

Current - Maximum per Contact

18A

Material Info

Reference - Drawing Numbers

Application Specification

RAS-98172-001

Packaging Specification

PP-98172



Series  
image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

98172Series

Mates With

Harnessmaker specific

Use With

2.80mm (.110") UCC terminals (98898-series)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION