

Multi-Device Charging Station, 48 USB Ports, iPad and Android Tablets, White

MODEL NUMBER: **CS48USBW**



Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 48 tablets and other USB devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Features

Fast Charging

- 48 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad®, Android™, Surface™ and Kindle™ tablets
- Also charges mobile phones and other USB devices
- Detachable 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug

Convenient Syncing

- USB sync uplink port connects to host computer for wired syncing
- Compatible with wireless syncing
- Supports simultaneous syncing and charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- Flow-through ventilation helps prevent devices from overheating
- Coated shelves shield devices from scratches and scuffs

Flexible Configuration

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor

Highlights

- Fast 2.4A USB charging, syncing and storage for 48 tablets
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Ships fully assembled and mounts to wall, desk, table or floor
- Detachable 10-ft. (3.05 m) power cord

Package Includes

- CS48USBW 48-Device USB Charging Station Cabinet, White
- Detachable 10-ft. (3.05 m) AC input cord w/NEMA 5-15P plug
- (2) Keys
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Door opens 180 degrees for improved device and service access
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates
- Converts to mobile cart with optional CSHANDLEKIT accessory (sold separately)

Specifications

OVERVIEW	
UPC Code	037332188960
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure; Sync
Device Compatibility	Tablet; Phone
Device Slots	48
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Voltage Compatibility (VAC)	110-240
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	48
Total Charging Amps	120A
Total Charging Watts	600
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(48) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Antimicrobial Coating	No
Charging Station Form Factor	Stationary Cabinet
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	104.19 x 72.01 x 67.01
Shipping Dimensions (hwd / in.)	41.02 x 28.35 x 26.38
Shipping Weight (kg)	86.64
Shipping Weight (lbs.)	191.00
Slot Dimensions - Bottom (hwd / in.)	8.0 x 0,8 x 13,9
Slot Dimensions - Bottom (hwd / mm)	204 x 20,1 x 353.8
Slot Dimensions - Middle (hwd / in.)	8.0 x 0,8 x 13,9
Slot Dimensions - Middle (hwd / mm)	204 x 20,1 x 353.8
Slot Dimensions - Top (hwd / in.)	8.1 x 0,8 x 13,9
Slot Dimensions - Top (hwd / mm)	206 x 20,1 x 353.8
Unit Dimensions (hwd / cm)	90,42 x 59,9 x 54,86
Unit Dimensions (hwd / in.)	35.6 x 23.62 x 21.6
Unit Weight (kg)	68.04
Unit Weight (lbs.)	150
Number of Shelves	3
ENVIRONMENTAL	
Power Consumption (Watts)	224
SPECIAL FEATURES	
Cord Management	Yes
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>