



**Part Number :** [1300062461](#)

**Product Description :** Mini-Change A-Size Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow TPE Cable, 8.0m (26.25') Length

**Series Number :** 130006

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 103006K13M080

---

## Documents and Resources

### Drawings

[1300062461\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

### UKCA - Declaration of Conformity

### CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow TPE Cable, 8.0m (26.25') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	78172552148

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	10.41mm (.410")
Cable Length	8.0m (26.25')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	899.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16

---

This document was generated on Dec 30, 2025