





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/02/12	

APPROVED: _____

DATE: _____ TITLE: _____



Panel hole dimensions



SPECIFICATIONS:

Material: Nylon66, rated UL 94V-2

Insulator color: Natural

Electrical:

Voltage Rating: 600V Max.

Current rating: 11 Amps Max.

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 5,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				HOUSINGS, MALE, VERTICAL			
HOLES				TITLE			
.X ± .10				.250 [6.35MM] PITCH CONNECTOR, 6 POS			
.XX ± .020				SIZE			
.XXX ± .015				PART NO.			
APPROVALS				DME-M-06-SQ			
DATE				REV.			
DRAWN				10/02/12			
CHECKED				10/02/12			
APPROVED				X			
REF:				S00123T			
SCALE:				NTS			
SHEET				1 OF 2			

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

HOUSINGS, MALE, VERTICAL

DME-M-06-SQ

6

5

4

3

2

1

6

5

4

3

2

1

D

D

C

C

B

B

A

A