

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301030064

Status:

Active

Overview:

Hand Lamps

Description:

Watertite Wet Location Incandescent Hand Lamp Only, 100W with TEFLON Globe



Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR85374
UL	E59251
General	
Product Family	Portable Lighting
Series	130103
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Outlet	None
Overview	Hand Lamps
Product Name	Watertite
Type	Hand Lamps
UPC	78678861330
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	127.00mm (5.000")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	254.00mm (10.000")
Length	N/A
Material - Globe	PTFE
Material - Guard	N/A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC
Material Info	
Engineering Number	1220

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130103 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION