


Connector Component			Connector Strip Dimension			Wire Spec.	Terminal ROJ & Strip		
Color	Component	Qty	Strip	ROJ	Color	SJT 14AWGX3C 105 °C BLACK Length: 1000±20 mm	Strip	ROJ	Color
40P BK 90±5 °A	IEC 320 C13 (LT-511R(15A 250V))	1	7±1	20±3	Black		5⁄8" (16mm)	2" (50.8mm)	Black
Copper	computer power cord terminals	3	7±1	20±3	White		5⁄8" (16mm)	2" (50.8mm)	White
White	(511 Inner Body)	1	7±1	20±3	Green		5⁄8" (16mm)	2" (50.8mm)	Green

			4. APPROVALS : UL, C-UL 5. Supplier for flexible cord : RHYTHM 6. Hi-Pot Test:2000v/1min<1mA>					
			DRAWER	Aaron	DATE	20/10/23	P/N	800-1403-2-SJT0-BL-00100-1
			APPROVE		REV.	0	Dr.No.	1091089
					比例		TOL.	±5mm
	DESCRIPTION	DATE					ALL DIMENSIONS IN mm	

CnC Tech

Industrial Cable and Connector Technology