



Connector Component			Connector Strip Dimension			Wire Spec.	Terminal ROJ & Strip		
Color	Component	Qty	Strip	ROJ	Color	SJT 16AWGX3C 105 °C BLACK Length: 1000±50 mm	Strip	ROJ	Color
40P BK 90±5"A	IEC 320 C13 (LT-511R(13A 250V))	1	7±1	20±3	Black		$\frac{5}{8}$ " (16mm)	2" (50.8mm)	Black
Copper	computer power cord terminals	3	7±1	20±3	White		$\frac{5}{8}$ " (16mm)	2" (50.8mm)	White
White	(511 Inner Body)	1	7±1	20±3	Green		$\frac{5}{8}$ " (16mm)	2" (50.8mm)	Green

RHYTHM: (UL)E88231 SJT 3X16AWG(1.31mm²)
105°C 300V VW-1 CSA LL54496 SJT
3X16AWG(1.31mm²)105°C 300V VW-1
RHYTHM R

	DESCRIPTION	DATE

5. Supplier for flexible cord: RHYTHM
6. Hi-Pot Test: 2000v/1min<1mA>

DRAWER	Eric	DATE	20/10/17	P/N	800-1603-2-SJT0-BL-00100-1
APPROVE		REV.	0	Dr.No.	1091058
		比例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

CnC Tech

Industrial Cable and Connector Technology