



Overview

Description	Design busway runs for uniquely shaped data centers.
Model Name	PB Busway Elbow Left, 225A, 600V max
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada , United States

Output

Nominal Output Voltage	208 3PH , , 600 3PH
Maximum Total Current Draw per Phase	225 A

Input

Nominal Input Voltage	208 3PH 415 3PH 600 3PH
Input Frequency	60 Hz

Physical

Net Weight	5.0 kg
Maximum Height	196.0 mm
Maximum Width	420.0 mm
Maximum Depth	420.0 mm
Shipping Weight	9.09 kg
Shipping Height	422.0 mm
Shipping Width	548.0 mm
Shipping Depth	598.0 mm
Color	Black

Environmental

Operating Environment	-10 - 40 °C
Operating Relative Humidity	0 - 95 %

Operating Elevation	0-3000 meters
Storage Temperature	-30 - 70 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-4500 meters

Conformance

Approvals	CSA , UL Listed , cUL Listed
Standard warranty	1 year (parts only)

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs