



Quality Products. Service Excellence.

2-Post Open Frame Rack *DNRRLDW Series*



Note: This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **DNRRLDK Series**. For alternative solution assistance, **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



When strength and reliability is the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

Features:

- Constructed in 12-gauge steel.
- Our automated tapping assembly provides EIA compliant 10-32 tapped rails **on the front** to ensure ease of mounting rack mount equipment.
 - Includes marked rack unit dividers to aid in equipment mounting.
- To keep the rack upright when loaded with equipment, we've included a large base for freestanding support. Optionally, the base can be caster mounted for moving the rack.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint.
- Before sending the DNRR on its way we cover the rails and base with a thick layer of cardboard to prevent any damage that may occur during transportation.
- Tested to nearly double the suggested static load rating of 850 lbs (386 kg).
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Cable Managers
- Hinged Clear Security Cover
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Adjustable Rack Mount DIN Rail Kit
- Open Frame Rack and Rack Cabinet Joining Kit
- Grounding & Bonding
- PDUs and Outlet Strips
- Rack Panels
- Universal Rack Shelf
- Two Post Centered Shelf
- Two Post Mounting Clamping Shelf
- Rack Unit Label
- Rack and Cabinet Caster Set
- 10-32 Mounting Hardware

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
DNRR42LDW	44.60	20.00	19.78	24U	42.00	19.00
DNRR63LDW	65.60	20.00	19.78	36U	63.00	19.00
DNRR70LDW	72.60	20.00	19.78	40U	70.00	19.00
DNRR77LDW	79.60	20.00	19.78	44U	77.00	19.00

Part No.	Overall Dimensions			Rack	Mounting Dimensions	
	Height	Width	Depth	Units	Height	Width
DNRR84LDW	86.60	20.00	19.78	48U	84.00	19.00

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.