




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/13	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Insulator: PA66, rated UL 94V-0
Insulator color: Green
Contact: Brass, Tin plated
Electrical:
Operation voltage: 300 VAC max
Current rating: 15 Amps
Contact resistance: 20 Mohms max
Insulation resistance: 500 Mohms min @ 500 VDC
Dielectric withstanding voltage: 2,000 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant.

Positions: 02 thru 24
A = .197 [5.00] x No. of Positions
B = .197 [5.00] x No. of Spoces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

EURO BLOCK, .197 [5.00] PITCH, VERTICAL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED				TITLE	
INCHES	HOLES				
.X ± .10	ØX ± .10				
.XX ± .020	ØXX ± .015				
.XXX ± .015	ØXXX ± .010				
APPROVALS				DATE	
DRAWN	AY		11/7/13		
CHECKED	NP		11/7/13		
APPROVED					
				SIZE	PART NO.
				X	EBPA-XX-C
				REF: S0067C	SCALE: NTS
				SHEET 1 OF 1	

