

Part Number : [1300190018](#)

Product Description : Die Block 4 Pole Angle Receptacle, Orange

Series Number : 130019

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : 43301



Documents and Resources

Drawings

[1300190018 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130019
Description	Die Block 4 Pole Angle Receptacle, Orange
IP Rating	N/A
Product Name	Die Block
Type	Die Block
UPC	78678843301

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC

Physical

Coupling Type	Push to Lock
Gender	Female
Keyway	None
Length	N/A
Material - Component	Nitrile/PVC
Mounting Thread Size	N/A
Net Weight	194.137/g
Orientation	N/A
Panel Mount	Front
Poles	4

Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

This document was generated on Dec 31, 2025