



NYS228BG

3 pole 1/4" plug, long diecast handle, black handle, gold plated contacts



Technical Information [hide](#)

Product	
Title	NYS228BG
Connection Type	Plug
Gender	male
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Contact resistance	depends on mating connector
Rated current	depends on mating connector
Mechanical	
Cable O.D.	≤ 6 mm
Lifetime	1000 mating cycles
Wiresize	24 AWG
Material	
Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black
Strain relief	Crimp type SnCe plated
Insulation	Thermoplastic

Environmental

Solderability

Complies with IEC 68-2-20

Temperature range

-20 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN[®]
REAN a brand of Neutrik AG