



**Part Number :** [395066008](#)

**Product Description :** 3.50mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Green Housing, 8 Circuits

**Series Number :** 39506

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip

---

## Documents and Resources

### Drawings

[395066008\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)6375-DC (05 Nov 2025) SCIP:d552555b-293f-4248-bb57-8fefc2b5787c
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39506
Description	3.50mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Green Housing, 8 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350452991

### Agency

UL	E48521
----	--------

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

## Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Green
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
PCB Thickness - Recommended	2.50mm
PC Tail Length	3.50mm
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
3.50mm Pitch Eurostyle Horizontal Plugs	<u><a href="#">39504</a></u>
3.50mm Pitch Eurostyle Vertical Plugs	<u><a href="#">39507</a></u>
Mates With	Most 3.50mm Pitch Industry Standard Plugs

---

This document was generated on Dec 16, 2025