

Data Sheet | Item Number: 280-369
Intermediate plate; 1.1 mm thick; orange

<https://www.wago.com/280-369>



Color: ■ orange

Physical data

Width	1.1 mm / 0.043 inches
Height	74 mm / 2.913 inches
Depth	33.5 mm / 1.319 inches

Material data

Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.067 MJ
Weight	2.6 g

Environmental requirements

Processing temperature	-35 ... +85 °C
Continuous operating temperature	-60 ... +105 °C

Commercial data

Product Group	1 (Rail Mounted Terminal Blocks)
PU (SPU)	100 (25) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332226561
Customs tariff number	85389099990



Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 280-369	↓

Documentation			
Bid Text			
280-369	19.02.2019	xml 2.57 KB	↓
280-369	28.04.2017	doc 23.50 KB	↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 280-369 ↓	EPLAN Data Portal 280-369 ↓
	WSCAD Universe 280-369 ↓
	ZUKEN Portal 280-369 ↓

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com