
PV2 Series Anti-vandal Switch



Applications / Markets


Audio / Visual


Security Devices


Industrial Controls


Kiosks


Electrical Housewares


Medical Equipment

Specifications

Electrical Rating: 2A, 48VDC
Mechanical Life: 1,000,000 Cycles
Electrical Life: 200,000 Cycles
Contact Resistance: 50mΩ Max.
Insulation Resistance: 1000 MΩ Min.
Dielectric Strength: 2,000VAC
Operating/Storage Temperature: -20°C to 55°C
Travel: 2.50mm
Moisture Protection: IP65
Contact Arrangement: SPST Off-(On)
Actuation Force: 4 N
Panel Thickness: 1-6mm
Mounting Nut Torque: 0.8Nm

Features & Benefits

- **16mm panel cutout**
- **Solder or screw termination options**
- **Flat, high or domed actuator options**
- **IP65 rated**

Part Number Configurator


Series	Actuator Options	Terminal Options	Function Options	Rating Options	Body Finish Options	Actuator Finish Options	Contact Material Options	Marking Options
PV2	**F** - Flat **H** - High **S** - Domed	**2** - Solder **6** - Screw	**4** - Off - (On)*	**0** - 2A, 48VDC	**G** - Gold **N** - Nickel **S** - Polished Stainless **B** - Brushed Stainless **1** - Black Anodized	**G** - Gold **N** - Nickel **S** - Polished Stainless **B** - Brushed Stainless **1** - Black Anodized	**NONE** - Silver **G** - Gold	**NONE** - Non-Illuminated **M01** - Power Symbol


NOTES:
*(ON) Denotes function is momentary


Specifications subject to change without notice 6.10.2020

Downloaded from Arrow.com.


SOLDER TERMINATION









SCREW TERMINATION








Downloaded from Arrow.com.

Actuator Options




Flat Actuator

High Actuator

Domed Actuator

Graphic Options



None

M01PowerSymbol

Downloaded from Arrow.com.